

SV75

3-Way Universal Diaphragm Isolation Valve



Valcor Engineering Corporation



DESCRIPTION





The SV75 series universal 3-way miniature diaphragm isolation valves provide high purity isolation of the media from the valve mechanism by excluding all metal components from the fluid path. Only PTFE or PEEK are in contact with the media. This design enables these valves to handle extremely corrosive or high purity liquids and gases without breaking down or contaminating the purity of the media. They are normally closed or normally open. These direct acting valves do not require system pressure to operate, and can control pressure and vacuum. The compact size, low weight and low power coils allow these valves to be used portable and benchtop instruments.

APPLICATION



The SV75 series are designed for analytical and medical instruments requiring the total isolation of the media from the valve mechanism. Low internal volume makes purging and sterilization between media batch changes fast and efficient. Applications include: blood analyzers and packaging equipment, analytical and medical instruments and equipment, clinical instruments, reagent and diluent dispensers, and printing inks, dyes, and colorants.

FEATURES

- Low power consumption is ideal for portable battery powered instruments
- 30 PSIG max pressure, optional 100 PSIG available
- 28" Hg vacuum
- Low internal volume
- Universal operation, inlet pressure at any port
- Low power 12 and 24 VDC coils rated for continuous duty
- 1/4-28 zero dead volume ports
- Convenient panel mounting holes in solenoid
- Mountable in any orientation
- Fully customizable for your application



Round Body
SV75P25T, SV75P60T-R,
SV75P48T-R



*3-Way Only

Custom designs are our specialty. Contact us today to see how we can help on your next project.

Valcor Engineering Corporation
2 Lawrence Road | Springfield, NJ 07081
(973) 467-8400 | scientific@valcor.com
www.valcor.com

Valve Parts in Contact with Fluid

Body	PTFE
Diaphragm	PTFE

Other Parts

Armature	430F SS
Spring	303 SS
Coil Housing	Nickel Plated Steel
Base Plate	Nickel Plated Steel

Body is also available in PEEK and PCTFE. Consult factory for availability of specific constructions.

Envelope Dimensions

Model Number (Round)	A (in.)	B (in.)	C	D	E	F	G	H
SV75P61T	0.75	1.161	0.5	#2-56	0.363	0.50	#2-56	N/A
SV75P25T	1.00	1.493	0.687	#4-40	0.45	0.687	#4-40	N/A
SV75P60T-R	1.25	1.78	0.884	#4-40	0.5	0.884	#4-40	N/A
SV75P48T-R	1.5	2.100	1.125	#4-40	0.563	1.125	#4-40	N/A

Model Number (Octagonal)	A (in.)	B (in.)	C	D	E	F	G	H
SV75P60T	1.25	1.814	0.884	#4-40	0.5	0.844	#4-40	1.5
SV75P48T	1.5	2.039	1.125	#4-40	0.562	1.125	#4-40	1.75

Note: P60 and P48 HP bodies are round.
All HP valves have PEEK bodies.

Specifications

Port Size	Orifice Size (ins.)	Max. Pressure (PSI)		Model Number	Voltage	Wattage	Internal Volume (µl)
		Gas & Liquid	Vacuum (in. Hg)				
SV75 3-Way Valve							
10-32	0.040"	30	28	SV75P61T-1	12 VDC	1.0	12
1/4-28	0.062"	30	28	SV75P25T-1	12 VDC	1.5	58
1/4-28	0.095"	30	28	SV75P60T-1**	12 VDC	4.2	121
1/8" NPS*	0.156"	30	28	SV75P48T-1	12 VDC	7.2	399
10-32	0.040"	30	28	SV75P61T-2	24 VDC	1.0	12
1/4-28	0.062"	30	28	SV75P25T-2	24 VDC	1.5	58
1/4-28	0.095"	30	28	SV75P60T-2**	24 VDC	4.2	121
1/8" NPS*	0.156"	30	28	SV75P48T-2	24 VDC	7.2	399

For Temperature and Duty Cycle information, please consult "Temp and Duty Cycle" link under Technical Information on our website. Alternate voltage of 6 VDC & 115V/60 HZ available upon request. Please consult factory for availability & part number.

High pressure version available up to 100 PSI ('-HP'). PEEK body only. Please consult factory for availability of specific constructions.

*1/8"-27 NPS (National Pipe Straight) thread. Flat bottom.

**Suffix part number with '-R' for round body.